Powerful, compact, electronic flushing unit with oil-free compressor. For flushing with water or a water/air mixture, disinfection, cleaning, preservation of pipe systems and for operation of pneumatic tools.

Flushing and desilting

Water pressure pipe network  $p \le 1 \text{ MPa}/10 \text{ bar}/145 \text{ psi}$ Pipe diameter installation  $\le DN 50, 2$ "

Disinfection of drinking water installations

Cleaning and preservation of radiators and area heating systems

Water temperature  $5-35^{\circ}$ C Water flow  $\leq 5 \text{ m}^3/\text{h}$ 

Operation of pneumatic tools

Operating pressure  $p \le 0.8 \text{ MPa/8 bar/116 psi}$ Suction rate  $\le 230 \text{ Nl/min}$ 

REMS Multi-Push S – Flushing with water or a water/air mixture. Easy switching of the air supply during the flushing process when desilting. Permanent process monitoring. Logging. USB interface.

## Universal use

Only **one** device for flushing with water or a water/air mixture, disinfection, cleaning, preservation of pipe systems, e.g. for desilting, cleaning and preservation of radiators and area heating systems, flushing and disinfection of drinking water installations in accordance with EN 806-4:2010 and for operating pneumatic tools.

## Design

Powerful, compact, electronic flushing unit with oil-free compressor. Handy, easily portable, only 32 kg. Measuring and control devices for automatically running the flushing programs and for documenting the results. Safety devices for avoiding contamination of the pipe network by flow-back. Overpressure valve for pressure limiting. 5 µm condensation and particle filters. Large tubular steel frame as a compressed air tank. Two practical handles for easy carrying. Space-saving, folding handle grip for easy movement. Mobile tubular steel frame with two rubbertyred wheels for easy transport and 2 rubber feet for firm standing. Connecting cable with integrated personal protection switch (PRCD). 2 hooks for winding up the power cable. Captive seals for input and output of the REMS Multi-Push S to avoid contamination during transport and storage. Practical hood for protecting the machine during transport and storage as an accessory.

# Compressor

Proven, powerful, oil-free piston compressor with crank drive, with capacitor motor 230V, 1500W. Pressure gauge for displaying the air pressure in the compressed air tank. Emergency stop button.

### Hoses

Transparent Ø 1" suction/pressure hose, with fabric inlay, 1.5 m long, with 1" hose screw fittings, with caps, for flushing, disinfection, cleaning, preservation. Captive caps for the inputs and outputs of the hoses to avoid contamination during transport and storage. Connecting hose compressor/water connections, 0.6 m long, with quick coupling DN 7.2 and 1" hose screw fitting, 1" double nipple, for blowing out water remains from REMS Multi-Push S and suction/pressure hoses at the end of work.

## Input and control unit

Easy desilting operation by buttons to switch over the air supply during the flushing process. Menu-guided input and menu-guided control for flushing drinking water installations according to EN 806-4:2010 with the possibility for the user to change the factory-set default values for adaptation to the applicable national safety provisions, rules and regulations for the application site. Format selection for date and time and selection of the different units. Input and control unit with 3" display with modern LCD technology, 76 mm screen diagonal,  $128\times64$  pixels. Permanent process monitoring during the program sequences. USB port for USB stick or printer. The respective latest version software for the input and control unit is available via USB stick as a download under www.rems.de > Downloads > Software.







German Quality Product



### **Desilting and flushing**

Buttons for easy switching of the air supply during the flushing process when desilting radiator and flat heater systems with the following possibilities: (1) without compressed air, (2) intermittent compressed air, (3) constant compressed air.

## Flushing according to EN 806-4

Flushing of drinking water installations with water or with a water/air mixture with intermittent compressed air in accordance with EN 806-4:2010 and information leaflet "Flushing, Disinfection and Commissioning of Drinking Water Installations" (August 2014) of the German Central Association for Sanitary, Heating and Air Conditioning (ZVSHK).

### **Disinfection**

REMS V-Jet TW disinfection unit for disinfection of drinking water installations in accordance with EN 806-4:2010 and information leaflet "Flushing, Disinfection and Commissioning of Drinking Water Installations" (August 2014) of the German Central Association for Sanitary, Heating and Air Conditioning (ZVSHK) and other pipe systems, as an accessory. REMS Peroxi Color, consisting of a 11 bottle of REMS Peroxi dosing solution for disinfection of approx. 1001 line volume and 20 ml bottle of red REMS Color dye for dyeing the dosing solution for filling and wash-out check, pipette for checking the effectiveness of the dosing solution, as an accessory. Feeding of the disinfectant solution without additional dosing pump (Patent EP 2 954 960).

## Cleaning and preservation

REMS V-Jet H cleaning and preservation unit for cleaning and preserving radiators and area heating systems, as an accessory. Cleaner, dyed green for filling and wash-out check and corrosion protection, dyed blue for filling check, for approx. 100 I line volume respectively, as an accessory. Feeding of cleaner and corrosion protection without additional dosing pump (Patent EP 2 954 960).

## Operation of pneumatic tools

Connection for pneumatic tools up to an air requirement ≤ 230 Nl/min, adjustable, for adaptation to the pneumatic tool being used. Pressure gauge for controlling the air pressure supplied by the compressed air tank. Pneumatic hose with quick coupling DN 7.2, as an accessory.

### Logging

Results of the flushing programs are saved with date, time and log number in the selected language and can be transferred to USB stick or printer for documentation. Printer as an accessory. Additions to saved data, e.g. customer name, project number, tester, are possible on external devices (e.g. PC, laptop, tablet-PC, Smartphone).



## Supply format

**REMS Multi-Push S Set.** Electronic flushing unit with oil-free compressor. For flushing with water or a water/air mixture, disinfection, cleaning, preservation of pipe systems, e.g. for desilting, cleaning and preservation of radiators and area heating systems, flushing and disinfection of drinking water installations and for operation of pneumatic tools  $\leq 230$  Nl/min. Input and control unit. Piston compressor with crank drive, capacitor motor 230 V, 50 Hz, 1,500 W, person circuit breaker (PRCD). Mobile tubular steel frame. Fastenings for water input and output of the REMS Multi-Push S. Two  $\emptyset$  1" suction/pressure hoses, with fabric inlay, 1.5 m long, with 1" hose screw fittings, with caps. Connecting hose compressor/water connections, 0.6 m long, with quick coupling DN 7.2 and 1" hose screw fitting. 1" double nipple, for blowing out water remains from REMS Multi-Push S and suction/pressure hoses at the end of work. Without disinfection unit, without cleaning and preservation unit. In a carton

cicarring and preservation and in a carton		
	ArtNo.	€
	115810 R220	2.480,82

Other voltages on request.



Description	ArtNo.	€
Fine filter with fine filter cartridge 90 μm, washable, with large dirt collection vessel	115609R	123,52
Fine filter cartridge 90 $\mu m$ , for fine filter with fine filter cartridge 90 $\mu m$	043054	40,07
Compressed air hose Ø 14 mm, 1.5 m long, with quick couplings DN 7.2 (plug, socket), for connecting pneumatic tools	115621R	61,97
Ø 1" suction/pressure hose, with fabric inlay, 1.5 m long, with G 1" screw fittings for flushing, disinfection, cleaning, preservation and pressure testing with water.	115633R	59,27
<b>Double nipple 1"</b> , for connecting 2 suction/pressure hoses and blowing out the suction/pressure hoses	045159	10,38
<b>Printer</b> for printing the stored results of the flushing and test programs, 1 roll of paper, USB connecting cable, power supply/charger Ni-Mh 100 – 240 V, $50-60$ Hz, $3$ W	115604R	508,62
Paper roll, pack of 5 for printer	090015R	18,89
Case with inlays for printer, paper rolls and other accessories	115703R	70,58
REMS V-Jet TW, disinfection unit for drinking water installations, for feeding dosing solution for disinfection REMS Peroxi Color, 11 bottle of REMS Peroxi dosing solution for disinfection of approx. 1001 line volume, 20 ml bottle of red REMS Color dye for dyeing the	115602R	304,13
dosing solution for filling and wash-out check, pipette for checking the effectiveness of the dosing solution.	115605R	82,00
Test strips $H_2O_2$ 0 – 1,000 mg/l, pack of 100, for checking the concentration of the disinfection solution	091072	71,21
Test strips $H_2O_2$ 0 – 50 mg/l, pack of 100, for checking the complete flushing out of the disinfection solution after disinfection	091073	71,21
<b>REMS V-Jet H</b> , cleaning and preservation unit for radiators and area heating systems, for feeding cleaner and corrosion protection.	115612R	304,13
REMS CleanH 1 l bottle of cleaner for radiators and area heating systems, dyed green for filling and wash-out		
check, for approx. 100 l line volume.	115607R	57,09
<b>REMS NoCor</b> 1l bottle of corrosion protection for preservation of radiators and area heating systems, dyed blue for filling check, for approx. 100 l line volume.	115608R	61,24
Hood for protecting the machine during transport and storage	115677 R	39,24
XL-Boxx system case for hoses	579600RMP	198,26



All prices excl. VAT