Electric decalcifying pump

REMS Calc-Push



REMS Calc-Push – effective electric decalcifying. High displacement.

Universal use

For effective decalcifying of pipes and containers, e.g. flow heaters, boilers, hot water tanks, cold water tanks, heat exchangers, heating and cooling systems.

Robust, compact, light, weights just 9.2 kg. Impact-proof plastic container for the decalcifying solution, useful container volume 21 I, with practical screw-on cap for closing the plastic container during transport. Flexible 1/2", 2.3 m long flexible PVC fabric hoses, with hose screw fittings with Rp ½" female thread and caps. 3-way lever for reversing the flow direction to remove even heavy lime deposits from both sides, with zero setting to interrupt the flow. Easy to carry due to centrally arranged handle with practical hose holders.

Unscrewable pump unit

Compact pump unit, consisting of a centrifugal pump and condenser motor, unscrewable, for easy cleaning of the pump unit and the plastic container after the decalcifying process. Self-sucking centrifugal pump, suitable for different decalcifying solutions of acetic acid, sulphuric acid, citric acid, formic acid, phosphoric acid, sulfamic acid. With proven, powerful condenser motor with quiet running, 165 W, on/off switch. High displacement ≤ 30 l/min for effective decalcifying.



Useful container volume 21 I

Displacement ≤ 30 I/min

Temperature of decalcifying

Displacement pressure ≤ 0.1 MPa/1.0 bar/15 psi Transport height ≤ 10 m

solution ≤ 50°C

REMS Calc-Push. Electric decalcifying pump for effective decalcifying of pipes and containers, e.g. flow heaters, boilers, hot water tanks, cold water tanks, heat exchangers, heating and cooling systems. Displacement ≤ 30 l/min, useful container volume 21 l. Pump unit with condenser motor 230 V, 50 Hz, 165 W. Displacement pressure ≤ 0.1 MPa/1.0 bar/15 psi. Transport height ≤ 10 m. Flexible ½", 2.3 m long flexible PVC fabric hoses, with hose screw fittings with Rp ½" female thread and caps. 2 double nipples ¾"-½", 2 double nipples ½"-¾". In a carton. Art -No. 115900 R220

Sale through specialist dealers.



REMS (UK) Ltd.

Unit 5 · Ash Industrial Estate Flex Meadow · Harlow · Essex CM19 5TJ

Phone +44 12 79 41 36 98 +44 12 79 41 37 04 www.rems.de · GBR@rems.de



www.rems.de



www.youtube.com/remstools



www.facebook.com/remstools



www.twitter.com/remstools



www.instagram.com/remstools